

Model No.	POS.1	POS.2	POS.3
2UD3	ON	OFF	ON
Term. Comm.	2-3,5-6	OPEN	2-1,5-4
SCHEMATIC			

SWITCH FUNCTION


SPECIFICATIONS

- MECHANICAL LIFE:** 40,000 make-and-break cycles.
- CONTACT RATING:** 0.4 VA max. @ 20 V AC or DC max.
- CONTACT RESISTANCE:** Below 100 mΩ typ. initial @ 2-4 V DC, 100 mA.ⓐ
- INSULATION RESISTANCE:** 1,000 MΩ mln.
- DIELECTRIC STRENGTH:** 500 Vrms mln. @ sea level.
- OPERATING TEMPERATURE:** - 30°C±85°C

MATERIALS

- HOUSING AND BASE:** Glass filled nylon 6/6 or 4/6 , flame retardant, heat stabilized(UL94V-0)
- ACTUATOR:** Glass filled nylon 6/6 , flame retardant, heat stabilized(UL94V-0), with standard internal o-ring seal.
- STATIONARY CONTACTS:** Copper alloy, with gold plate over nickel plate.
- TERMINALS:** C268, with gold plate over nickel plate. ⓐ
- TERMINAL SEAL:** Epoxy. All terminals insert molded.

NOTE: Specifications and materials listed above are for switches with standard options. For information on specific and custom switches, consult Customer Service Center.



PC MOUNTING

德利威電子股份有限公司
DAILYWELL ELECTRONICS CO.,LTD.

符號	原尺寸	修改後尺寸	變更日期	SCALE (比例): 3:2	TITLE 圖名	Sealed Ultraminiature Toggle Switches		SIZE 圖紙	A4	
1	Ⓐ	Recommand 1.contact resistance 2.Switch support 3.Terminals	MAY-10-2005	TOLERANCE (公差): 0.00 mm ± 0.25mm 0.0 mm ± 0.40mm ANGULAR : ± 5° FILE NAME : 2UDP0003	DWG NO. 圖號	2UD3T1A1M2RE		UNIT 單位	inch mm	
2	Ⓑ	0.40	MAY-10-2005		REV. 版本	B	DATE 日期	NOV - 05 - 2004	SHEET 張數	1 of 1
3	Ⓒ				CHECKED BY 審核	RICHARD		DRAWN BY 製圖	BLUE	
4	Ⓓ									