




P.C.B LAYOUT  
TOLERANCE:±0.05



**Ordering Information:**

A3961WV-XP - \*\*\* - \*\* - \*\*  
1 2 3 4

1.Part NO.

2.Material:

(blank): Nylon 66,UL94V-2/Natural  
V0: Nylon 66,UL94V-0/White  
GWT: Nylon 66,UL94V-0(Beige),  
IEC 60335-1,5th Edition  
Glow Wire Capable.

3.Color:

BL:Blue GN:Green  
RD:Red YL:Yellow

4.Finish:

(blank):Tin over Nickel  
G:Gold over Nickel

**SPECIFICATIONS:**

Current Rating: 7A AC,DC  
Voltage Rating: 250V AC,DC  
Temperature Range: -40°C ~ +105°C  
Contact Resistance: 10mΩ Max  
Insulation Resistance: 1000MΩ Min  
Withstanding Voltage: 1500V AC/minute  
Pin Material: Brass  
Material: Nylon 66,UL94V-2

**Ordering Information & Dimensions**

Part NO.	Dimensions(mm)	
	A	B
A3961WV-2P	3.96	7.92
A3961WV-3P	7.92	11.88
A3961WV-4P	11.88	15.84
A3961WV-5P	15.84	19.80
A3961WV-6P	19.80	23.76
A3961WV-7P	23.76	27.72
A3961WV-8P	27.72	31.68
A3961WV-9P	31.68	35.64
A3961WV-10P	35.64	39.60
A3961WV-11P	39.60	43.56
A3961WV-12P	43.56	47.52
A3961WV-13P	47.52	51.48
A3961WV-14P	51.48	55.44
A3961WV-15P	55.44	59.40
A3961WV-16P	59.40	63.36
A3961WV-17P	63.36	67.32
A3961WV-18P	67.32	71.28
A3961WV-19P	71.28	75.24
A3961WV-20P	75.24	79.20
A3961WV-21P	79.20	83.16
A3961WV-22P	83.16	87.12
A3961WV-23P	87.12	91.08
A3961WV-24P	91.08	95.04

**CJTconn** CHANGJIANG CONNECTORS CO.,LTD.

Unit mm	Scale 3:1	Sheet 1 of 1	TITLE <b>3.96mm PITCH 180° WAFER</b>
DRWN Dengchun Yi	CHK'D Diankui Wan	APPR Jack Yin	DRAWING NO. <b>A3961WV-XP</b>
General Tolerances A1 A0 REV	THIRD ANGLE PROJECTION		REV A1

A1	ADD THE COLOR	2019.04.11
A0	NEW RELEASE	2005.05.10
REV	DESCRIPTION	DATE