








修订 REV	标记 MARK	修改摘要 REVISION DESCRIPTION	签名 SIGNATURE	日期 DATE
AO		NEW RELEASE	黄艳兰	2020-09-18



Specifications:

Contact resistance: $\leq 20m\Omega$
 Insulation resistance: $\geq 500M\Omega$
 Rated voltage: 100V AC DC
 Rated current: 2.0A AC DC (AWG#24)
 Withstand Voltage: 500V AC/minute
 Temperature Range: $-40^{\circ}C \sim +105^{\circ}C$
 Housing: LCP UL94V-0, Natural (Beige)
 Contacts: Phosphor Bronze/Sn-plated
 Solder Tabs: Brass/Sn-plated



孔位	尺寸				孔位	尺寸			
	A	B	C	D		A	B	C	D
2P	7.30	1.50	4.45	6.10	9P	17.80	12.00	14.95	5.00
3P	8.80	3.00	5.95	7.60	10P	19.30	13.50	16.45	5.00
4P	10.3	4.50	7.45	9.10	11P	20.80	15.00	17.95	5.00
5P	11.8	6.00	8.95	10.6	12P	22.30	16.50	19.45	5.00
6P	13.3	7.50	10.45	12.1	13P	23.80	18.00	20.95	5.00
7P	14.80	9.00	11.95	13.60	14P	25.30	19.50	22.45	5.00
8P	16.30	10.50	13.45	5.00	15P	26.80	21.00	23.95	5.00

Circuits	DIM. D	DIM. E	Q'ty/Reel	Packing (Reel/Caton)
02~03 PIN	-	16	700PCS	20/Reel
04~06 PIN	-	24	700PCS	15/Reel

HDGC 深圳市华德共创科技有限公司
 Shenzhen Huade co-create Technology Co.,LTD
 TEL : 0755-27111225 FAX : 0755-29940187

-TOLERANCES- UNLESS OTHERWISE SPECIFIED 公差参数表				TITLE: 产品名称: 1.5立贴				
X.X	±0.30	X.X°	±3°	APPD: 核准: 谢亮	PART NO: 产品编号: HDGC1501WVA-S-XP			
X.XX	±0.30	X.XX°	±2°	CHECK: 校对: 王建业	DATE	SCALE	UNIT	CODE NUMBER
X.XXX	±0.10	X.XXX°	±1°	DRAW: 绘图: 黄艳兰	2020-09-18	1:1	mm	A018