





TSSUE DATE	2018.05.15	OUR P/N	XR6*8-472K-短脚
------------	------------	---------	---------------

1. 外观尺寸图 DIMENSIOS



A=7.5MAX
B=10.0MAX
C= 3.5±5.0
D=Φ0.65±0.05
E=3.0±0.05

2. 接线图 CONNECTION (BOTTOM VIEW)



3. 绕线规格 WINDING SPEC

端子 TERMINZL	线 WIRE	圈数 TURNS	绕线方式 WINDING METHOD
S---F	Φ0.10 2UEW	410 TS (REF)	CLOSED

4. 电气特性 ELECTRONICS CHARACTERISTIC

客户代码 Part No.	厂方代码 OUR Part No.	电感量 Inductance at 1KHz	直流电阻 D. C. R max.	定格电流 I. D. C max.	标识 Marking	规格代码 Sample No.
	XR6*8-472K	4.7mH±10%	15 Ω	100mA	—	—

备注:

OPERATING TEMP. : -40°C ~ +85°C

INDUCTANCE DROP=10% TYP. AT IDC.

制作 DRW	审核 CHK	确认 APPD	东莞市祥如电子有限公司
洪碧华 2018.05.15	关菊花 2018.05.15	刘丰	



东莞市祥如电子有限公司
DONGGUAN XIANGRU ELECTRONICS CO., LTD

试产 (样) 报告

(TEST REPORT)

MODEL NO: 产品型号:	XR6*8-472K-短脚	EVALUATED Q' TY: 试样数:	10PCS
--------------------	---------------	--------------------------	-------

WATERIAL CODE: 磁材型号规格:	DR6.0*8.0	TESTED DATE: 试制日期:	2018.05.15
---------------------------	-----------	-----------------------	------------

SPC 规格	L (uH)	DCR (Ω)	MAX 15	SPC 规格	L (uH)	DCR (Ω)	MAX 15	SPC 规格	L (uH)	DCR (Ω)	MAX 15	SPC 规格	L (uH)	DCR (Ω)	MAX 15	SPC 规格	L (uH)	DCR (Ω)	MAX 15	
																				LOTS 序号
1	4.53	12.098																		
2	4.52	12.141																		
3	4.50	12.180																		
4	4.59	12.214																		
5	4.58	12.398																		
6	4.54	12.325																		
7	4.62	12.072																		
8	4.64	12.195																		
9	4.55	12.214																		
10	4.51	12.293																		
11																				
12																				

(DATA) 试样情况记录

REMARK: HM2801A HM2770A HP4342A VR-114 VR115
备注: 1KHz 0.25V
外观. 包装: 外套黑色UL套管, 1000PCS/包. OK

RESULTS: 判定:	制样员DRW	东莞市祥如电子有限公司
<input checked="" type="checkbox"/> 合格 (PASSED) <input checked="" type="checkbox"/> ROHS	洪碧华	
<input type="checkbox"/> 不合格, 改良后 (FAILED) 参照 (REF) _____	2018.05.15	