




规格承认


CUSTOMER		CUSTOMER'S P/S	
TSSUE DATE	2021.07.25	OUR P/N	XR0810-332K-短脚

1. 外观尺寸图 DIMENSIOS



A=9.5MAX
 B=11.5MAX
 C=4.0±0.5
 D=Φ0.6±0.05
 E=4.0±0.10

2. 接线图 CONNECTION (BOTTOM VIEW)



3. 绕线规格 WINDING SPEC

端子 TERMINZL	线 WIRE	圈数 TURNS	绕线方式 WINDING METHOD
S---F	Φ0.17 2UEW	310 TS (REF)	CLOSED

4. 电气特性 ELECTRONICS CHARACTERISTIC

客户代码 Part No.	厂方代码 OUR Part No.	电感量 Inductance at 1KHz	直流电阻 D. C. R max.	定格电流 I. D. C max.	标识 Marking	规格代码 Sample No.
	XR0810-332K	3.3mH±10%	6.0 Ω	160mA	---	---

备注:

OPERATING TEMP. : -40°C ~ +85°C

INDUCTANCE DROP=10% TYP. AT IDC.

制作 DRW	审核 CHK	确认 APPD	祥如电子
洪碧华	关菊花	刘丰	
2021.07.25	2021.07.25	2021.07.25	



东莞市祥如电子有限公司

DONGGUAN XIANGRU ELECTRONICS CO., LTD

试产 (样) 报告

(TEST REPORT)

MODEL NO: 产品型号: XR0810-332K-短脚	EVALUATED Q' TY: 10PCS 试样数:
-----------------------------------	--------------------------------

WATERIAL CODE: 磁材型号规格: DR8.0*10.0	TESTED DATE: 2021.07.25 试制日期:
--------------------------------------	----------------------------------

SPC 规格	L (uH) 3.3mH±10%	DCR (Ω) MAX 6.0								
			LOTS 序号							
(DATA) 试样情况记录	1	3.32	5.01							
	2	3.31	5.12							
	3	3.28	5.13							
	4	3.25	5.14							
	5	3.21	5.08							
	6	3.35	5.20							
	7	3.27	5.18							
	8	3.22	5.17							
	9	3.34	5.09							
	10	3.32	5.11							
	11									

REMARK: HM2801A HM2770A HP4342A VR-114 VR115
 备注: 1KHz 0.25V
 外观: 外套黑色UL套管 OK

RESULTS: 判定: <input checked="" type="checkbox"/> 合格 (PASSED) <input checked="" type="checkbox"/> ROHS <input type="checkbox"/> 不合格, 改良后 (FAILED) 参照 (REF) _____	制样员DRW 彭丽粉 2021.07.25	祥如电子
---	-------------------------------------	------