





TSSUE DATE	2022.04.29	OUR P/N	XR8*10-501K-短脚
------------	------------	---------	----------------

1. 外观尺寸图 DIMENSIOS



A=9.0MAX  
 B=11.5MAX  
 C=3.5±0.5  
 D=Φ0.6±0.05  
 E=4.0±0.10

2. 接线图 CONNECTION (BOTTOM VIEW)



3. 绕线规格 WINDING SPEC

端子 TERMINZL	线 WIRE	圈数 TURNS	绕线方式 WINDING METHOD
S---F	2-UEW /155℃ Φ0.25mm	126 TS (REF)	CLOSED

4. 电气特性 ELECTRONICS CHARACTERISTIC

客户代码 Part No.	厂方代码 OUR Part No.	电感量 Inductance at 1KHz	直流电阻 D. C. R max.	定格电流 I. D. C max.	标识 Marking	规格代码 Sample No.
	XR8*10-501K	500uH ±10%	0.9Ω	—	—	—

备注:

OPERATING TEMP. : -40℃~+85℃

INDUCTANCE DROP=10% TYP. AT IDC.

制作 DRW	审核 CHK	确认 APPD	
洪碧华	关菊花	刘丰	
2022.04.29	2022.04.29	2022.04.29	



东莞市祥如电子有限公司  
DONGGUAN XIANGRU ELECTRONICS CO., LTD

试产 (样) 报告

(TEST REPORT)

MODEL NO: 产品型号:				XR8*10-501K-短脚				EVALUATED Q' TY: 试样数:				10PCS			
WATERIAL CODE: 磁材型号规格:				DR8.0*10.0				TESTED DATE: 试制日期:				2022.04.29			
(DATA) 试样情况记录	SPC 规格	L (mH)	DCR (Ω)												
	LOTS 序号	500uH ±10%	MAX 3.9												
	1	0.575	0.763												
	2	0.583	0.767												
	3	0.581	0.770												
	4	0.583	0.755												
	5	0.580	0.765												
	6														
	7														
	8														
	9														
	10														
11															
REMARK: HM2801A HM2770A HP4342A VR-114 VR115															
备注: 1KHz 0.25V															
外观. 包装: 外套黑色PVC套管Φ8, 印字 (黑色).															
RESULTS: 判定:								制样员DRW							
<input checked="" type="checkbox"/> 合格 (PASSED) <input checked="" type="checkbox"/> ROHS <input type="checkbox"/> 不合格, 改良后 (FAILED) 参照 (REF) _____								洪碧华							
								2022.04.29							