




P.C.B LAYOUT  
BOTTOM VIEW



SCHEMATIC (NON-SHORTING)

- G-Switch Specification:**
1. Operating temperature range : -40 °C to +85 °C
  2. Rating : 50mA, 12V DC
  3. Insulation resistance : 100MΩ min, 100V DC
  4. Dielectric strength : 250V AC for 1 min
  5. Contact Resistance : 100m Ω max.

6	TERMINAL	COPPER ALLOY	Ag PLATING
5	SPRING	STAINLESS STEEL	
4	CAM STICK	STAINLESS STEEL	
3	CASE	NYLON	GREY
2	COVER	NYLON	BLACK
1	KNOB	NYLON	BLACK
NO.	PART NAME	MATERIAL	REMARK



SCALE: 4:1	UNIT: mm	Title: Push Switch 5.8x5.8x7.4mm		REV: A0	SHEET: 1/1
SIZE: A4	UNLESS OTHERWISE SPECIFIED	Mold Code: PS-5824WVB-2PN			
General Tolerance:		DRAWN	CHECKED	APPROVED	DATE
X	+0.30	Xia	Chen	Chen	2023.02.01
X.X	+0.20				
X.XX	+0.15				
X.XXX	+0.10				
Angles	±3°				



A B C D E