





1 2 3 4 5 6 7 8 9 10 11 12 13 14

SIDE	DATE	DESCRIPTION	APPROVER
▲			
▲			



RECOMMENDED PC BOARD LAYOUT
APPLICATIONS: PC BOARD THICKNESS=1.60mm



- 一、 MATERIAL:
- 1.Insulator:PBT+30%Glass Fiber (UL94V-0)
 - 2.Contact:Brass
 - 3.Contact Plated:Glod Flash over Tin Or Glod Plated Or Tin Plated
 - 4.Shell: Steel,Nickel Plated
- 二、 SPECIFICATION:
- 1.Current Rating:5 AMPS
 - 2.Insulation Resistance: 1000MΩ MIN. At 500VDC
 - 3.Dielectric Strength: 500V for One minute
 - 4.Operation Temperature: -55° C~+105° C.

电话 (tel)	公 差					
传真 (fax)	±0.25 ±0.13 ±0.02±0.05	±0.10 ±0.05 ±0.01	s			
比例 (scale)	1 : 1	日期 (date)	单位 (units)	mm	图 名 (name)	DR-15S 铆合锁螺丝
页次 (sheet)	A / 1	绘图 (draw)	颜色 (shaded)		图号 (draw number)	
版次 (rev.)	B	审核 (ch'k)	材料 (m't'l)		料号 (Part number)	
视图 (view)	⊕	核准 (app'd)	处理 (finish)		图档 (File Name)	

1 2 3 4 5 6 7 8 9 10 11 12 13 14