





REV.	LOCAS.	DESCRIPTION	DATE	DRAWN
A	NEW	INITIAL RELEASE.	2013.04.12	吳才仙



Specifications
 Current Rating:3Amp
 Insulation Resistance:1000MΩMin.
 Dielectric Withstanding Voltage:600VAC
 Contact Resistance:20mΩMax.
 Operating Temperature:-40°C to +105°C
 Materials
 Contact Material:Phosphor Bronze
 Insulator Material:High Temperature Thermoplastic, UL 94V-0 LCP or the equivalent material
 All materials must meet Greenconn requirement for environment protection.

Recommended P.C.Board
 Layout
 (Tolerance:±0.05)



Ordering Information

C SHC101 - XX XX A 012 C 1 A X

- No. of Pins per Row: 02~40
- Standard Plating: 02=Gold Flash, 01=Tin, 05=Gold Flash/Tin
- Color: 1=Black
- Standard Packing: C=Tube, A=Box, F=Cap+Tube
- Selective Plating

格 菱 股 份 有 限 公 司
Greenconn Corporation

REV.	UNIT.	SCALE.	PAGE.	GENERAL TOLERANCE	DESIGN:	DATE:	DWG. NO.	TITLE.
A	mm	4:1	1/1	X.±5.0° .X.±3.0° .XX±2.0° .XXX±1.0°	吴才仙	2013.04.12	CSHC101-CA12CA	2.54 FEMALE HEADER SINGLE ROW SMT TYPE CONNECTOR
				X.±0.30 .X±0.25 .XX±0.15 .XXX±0.10	钟毓明	2013.04.12		
					林葛辉	2013.04.12		
					李辉	2013.04.12		
					李辉	2013.04.12	CSHC101-XXXX A012C1AX	

1 2 3 4 5 6 7 8 9

A B C D E F