



REV.	LOCAS.	DESCRIPTION	DATE	DRAWN
01	NEW	INITIAL RELEASE:	2010.09.09	黎華明
02	△	依上級要求變更圖號	2012.05.04	李芳忠

Specifications
 Current Rating: 3Amp
 Insulation Resistance: 1000MΩ/Min.
 Dielectric Withstanding Voltage: 600VAC
 Contact Resistance: 20mΩ/Max.
 Operating Temperature: -40°C to +105°C
 Materials
 Contact Material: Phosphor Bronze
 Insulator Material: High Temperature Thermoplastic, UL 94V-0 LCP or the equivalent material
 All materials must meet Greenconn requirement for environment protection.



Recommended P.C.Board
 Layout
 (Tolerance: ±0.05)



Ordering Information

C SHC205 - XX XX A 004 C 1 A X

No. of Pins per Row: 02~40
 Standard Plating: 02=Gold Flash, 01=Tin
 Color: 1=Black
 Standard Packing: C=Tube, Selective Packing: A=Box, F=Capp+Tube, E=Capp+T&R, G=Acetate Tape+Tube, H=Acetate Tape+Tube&Reel

Dim.C	NOTE
4.00mm	02~03Pin
10.15mm	04~40Pin

GENERAL TOLERANCE

X.±5.0°	X.±0.30
.X.±3.0°	.X.±0.25
.XX.±2.0°	.XX.±0.15
.XXX.±1.0°	.XXX.±0.10

DESIGN: 李芳忠 DATE: 2012.05.04

CHECKED: 劉北平 DATE: 2012.05.04

AUDITED: 李輝 DATE: 2012.05.04

APPROVED: cc_li DATE: 2012.05.04

DWG. NO. △ CSHC205-CA4CA

PART NO. CSHC205-XXXX A004C1AX

TITLE: 2.54 FEMALE HEADER
 DUAL ROWS SMT TYPE
 BASE 8.50H

格 菱 股 份 有 限 公 司
Greenconn Corporation

REV.	UNIT.	SCALE.	PAGE.
02	mm	4:1	1/1

A 1 2 3 4 5 6 7 8 9