





REV.	LOCAS.	DESCRIPTION	DATE	DRAWN
01	NEW	BATCH PRODUCTION INITIAL RELEASE.	2022.03.28	何東華

Specifications
 Current Rating:3Amp
 Insulation Resistance:1000MΩMin.
 Dielectric Withstanding Voltage:600VAC
 Contact Resistance:20mΩMax.
 Operating Temperature:-40°C to +105°C
 Materials
 Contact Material:Brass
 Insulator Material:High Temperature Thermoplastic, UL 94V-0 LCP or the equivalent material
 All materials must meet Greenconn hazardous substances control standards.



Recommended P.C.Board Layout
 (Tolerance:±0.05)



Ordering Information

G PHD207 - XX XX A 001 C 1 B X

No. of Pins per Row 02~30
 Standard Plating 02=Gold Flash
 Selective Plating 01=Tin 05=Gold Flash/Tin

Color 1=Black

Standard Packing C=Tube(04~30PIN)
 Selective Packing D=Tape Reel E=CAP+Tube(04~30PIN) F=CAP+Tape&Reel

Greenconn
 Website:www.greenconn.com
 E-mail:sales@greenconn.com

3RD.ANG PROJ.

 PAGE. 1/1

GENERAL TOLERANCE	
X'±5.0'	X.±0.30
.X'±3.0'	.X±0.25
.XX'±2.0'	.XX±0.15
.XXX'±1.0'	.XXX±0.10

DESIGNED: 何東華 DATE: 2022.03.28
 CHECKED: 张春进 DATE: 2022.03.28
 APPROVED: 邱國廷 DATE: 2022.03.28

DWG. NO. GPHD207-CA1CB
 PART NO. GPHD207-XXXX A001C1BX

TITLE. 2.54 PIN HEADER DUAL ROWS SMT TYPE CONNECTOR