



- NOTES:
- MATERIAL:
    - HOUSING: PA9T. COLOR IS BLACK;
    - CONTACT: PHOSPHOR COPPER (C5191,T=0.25mm);
  - ELECTRICAL:
    - VOLTAGE RATING: 30 VAC RMS;
    - CURRENT RATING: 0.5 AMP;
    - CONTACT RESISTANCE: 30MILLIOHMS MAX.;
    - WITHSTAND VOLTAGE: 500 VAC RMS  
50(60)Hz,1MIN.;
    - INSULATION RESISTANCE: 100MEGOHMS MIN  
@500V DC;
  - MECHANICAL:
    - MATING FORCE: 5~25N;
    - UNMATING FORCE: 5~25N;
    - OPERATING LIFE: 5000 CYCLES;
  - PLATING:
    - TERMINAL:  
NI PLATING OVER ALL,  
TIN PLATING ON SOLDER AREA,
  - ENVIRONMENTAL:
    - STORAGE TEMPERATURE RANGE: -40°C~+85°C;
    - OPERATION TEMPERATURE RANGE: -25°C~+70°C;
    - SALT SPRAY TEST:8H(EXCLUDING RIVETED BENDS)

序号	品名	材质	电镀/颜色	备注
A	底座	PA9T	黑色	
B	端子	C5191	焊区镀锡 全周镀镍	

			GENERAL TOLERANCE	制图 DRAWING	深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD			
			DIM TOL	审核 CHECK	产品名称 TITLE	313耳机3节贴片 黑色	版本 REV.	A
			X.X ±0.30	批准 APPROVAL	产品料号 PART NO.	HC-PJ-3133-6P-S	单位 UNITS	mm
1	初版发行		X.XX ±0.20	比例 SCALE	材料 MATERIAL		页次 SHEET	1/1
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	X.XXX ±0.10	投影 Projection				
			Angle ±3.0°					