




NOTES:

1. MATERIAL:
  - 1.1. HOUSING: PPA. COLOR IS BLACK;
  - 1.2. CONTACT: PHOSPHOR COPPER (C5191,T=0.2mm);
2. FINISH:
  - 2.1. TERMINAL:
    - CONTACT AREA: NI PLATED OVER ALL;
    - SOLDER AREA: SN PLATED OVER ALL;
3. ELECTRICAL:
  - 3.1. VOLTAGE RATING: 30 VAC RMS;
  - 3.2. CURRENT RATING: 0.5 AMP;
  - 3.3. CONTACT RESISTANCE: 30MILLIOHMS MAX.;
  - 3.4. WITHSTAND VOLTAGE: 500 VAC RMS  
50(60)Hz,1MIN.;
  - 3.5. INSULATION RESISTANCE: 100MEGOHMS MIN  
@500V DC;
4. MECHANICAL:
  - 4.1. MATING FORCE: 5~25N;
  - 4.2. UNMATING FORCE: 5~25N;
  - 4.3. OPERATING LIFE: 5000 CYCLES;
5. ENVIRONMENTAL:
  - 5.1. STORAGE TEMPERATURE RANGE: -40°C~+85°C;
  - 5.2. OPERATION TEMPERATURE RANGE: -25°C~+70°C;
6. SALT SPRAY TEST: 8H(EXCLUDING RIVETED BENDS)



序号	品名	材质	电镀/颜色	备注
A	基座	PPA	黑色	
B	端子	C5191	镀镍 镀锡	

			GENERAL TOLERANCE		制图		深圳市华灿天禄电子有限公司		
			DIM	TOL	DRAWING		ShenzhenhuacantianluELECTRONICS CO.,LTD		
			X.X	±0.30	审核		产品名称		版本
			X.XX	±0.20	CHECK		TITLE		REV.
			X.XXX	±0.10	APPROVAL		320D 红铜插件 黑色		A
			Angle	±3.0°	比例		产品料号		单位
1	初版发行	日期			SCALE		HC-PJ-320D-4P-S		UNITS
序号	变更内容	日期			投影		材料		页次
No.	MODIFY CONTENT	MODIFY DATE			Projection		MATERIAL		SHEET