




- NOTES:
- MATERIAL:
 - HOUSING: PPA, COLOR IS BLACK;
 - CONTACT: PHOSPHOR COPPER ;
 - FINISH:
 - TERMINAL:
 - CONTACT AREA: NI PLATED OVER ALL;
 - SOLDER AREA: SN PLATED OVER ALL;
 - ELECTRICAL:
 - VOLTAGE RATING: 30 VAC RMS;
 - CURRENT RATING: 0.5 AMP;
 - CONTACT RESISTANCE: 30MILLIOHMS MAX.;
 - WITHSTAND VOLTAGE: 500 VAC RMS
50(60)Hz, 1MIN.;
 - INSULATION RESISTANCE: 100MEGOHMS MIN
@500V DC;
 - MECHANICAL:
 - MATING FORCE: 5~25N;
 - UNMATING FORCE: 5~25N;
 - OPERATING LIFE: 5000 CYCLES;
 - ENVIRONMENTAL:
 - STORAGE TEMPERATURE RANGE: -40°C~+85°C;
 - OPERATION TEMPERATURE RANGE: -25°C~+70°C;
 - SALT SPRAY TEST: 8H(EXCLUDING RIVETED BENDS)



序号	品名	材质	电镀/颜色	备注
A	基座	PPA	黑色	
B	端子	磷铜0.25T	镀银	



GENERAL TOLERANCE			制图 DRAWING		深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO., LTD			
	DIM	TOL	审核 CHECK		产品名称 TITLE	320D 3.5耳机插座 贴片	版本 REV.	A
	X.X	±0.30	批准 APPROVAL		产品料号 PART NO.	HC-PJ-320D-3P-S	单位 UNITS	mm
1	初版发行		比例 SCALE		投影 Projection		页次 SHEET	1/1
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	Angle	±3.0°	材料 MATERIAL			