



PCB LAND DIMENSION
PCB电路板焊盘尺寸

SPECIFICATION

规范
 Rating: 50mA, 12V DC
 额定值: 50mA, 12V DC
 Insulation resistance: 100MQ min. 100V DC
 绝缘电阻: 100MQmin. 100V DC
 Dielectric strength: 250V AC for 1 min
 介电强度: 250V AC 1分钟
 Contact resistance: 100mΩ max
 Travel: 0.25±0.1mm
 行程: 0.25±0.1mm
 Lifetime: 600000 times
 寿命: 600000 times
 Operating force: 160±50gf
 操作力: 160±50gf
 Operating temperature rang: -30°C to + 85°C
 工作温度范围: -30°C to + 85°C



CIRCUIT DIAGRAM
电路图

5	Terminal 端子	Brass 黄铜	4	Ag plating 镀银
4	Base 基座	PA6T	1	Black 黑色
3	Contact 弹片	SUS	1	Ag plating 镀银
2	Stem 按钮	PA6T	1	Brown 棕色
1	Cover 盖板	Brass 黄铜	1	
NO 序号	Part name 部件名	Material 材料	QTY 数量	Remark 备注

A4				
A3				
A2				
A1				
REV	DATE	REVISION	DESCRIPTION	ISSUE
	A			B



COMMON TOLERANCE

X.XX	± 0.10
X.X	± 0.15
X	± 0.25

ANGULAR

UNIT	MM	PROJECTED		PRODUCT NAME:
DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP10721645
DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw
ROCPCU TECHNOLOGY CO., LTD				
Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission				
D	E	F	G	