



PCB LAND DIMENSION
PCB电路板焊盘尺寸

SPECIFICATION

规范
 Rating: 50mA, 12V DC
 额定值: 50mA, 12V DC
 Insulation resistance: 100MQ min. 100V DC
 绝缘电阻: 100MQmin. 100V DC
 Dielectric strength: 250V AC for 1 min
 介电强度: 250V AC 1分钟
 Contact resistance: 100mΩ max
 Travel: 0.25±0.1mm
 行程: 0.25±0.1mm
 Lifetime: 600000 times
 寿命: 600000 times
 Operating force: 260±50gf
 操作力: 260±50gf
 Operating temperature rang: -30°C to + 85°C
 工作温度范围: -30°C to + 85°C



CIRCUIT DIAGRAM
电路图

NO 序号	Part name 部件名	Material 材料	QTY 数量	Remark 备注
5	Terminal 端子	Brass 黄铜	4	Ag plating 镀银
4	Base 基座	PA6T	1	Black 黑色
3	Contact 弹片	SUS	1	Ag plating 镀银
2	Stem 按钮	PA6T	1	Dark red 暗红色
1	Cover 盖板	Brass 黄铜	1	

REV	DATE	REVISION	DESCRIPTION	ISSUE
A4				
A3				
A2				
A1				



COMMON TOLERANCE

X.XX	± 0.10
X.X	± 0.15
X	± 0.25

ANGULAR

UNIT	MM	PROJECTED	PRODUCT NAME:
DRAWN BY	FUYUAN	CHECKED BY	COCO
DATE	2019	APPROVAL B	ALEN
ROCPCU TECHNOLOGY CO., LTD			
Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission			

PRODUCT NAME:

MODEL NO: TP10722680

Https: www.rocpcu.tw