



PCB LAND DIMENSION  
PCB电路板焊盘尺寸

SPECIFICATION

规范  
 Rating: 50mA, 12V DC  
 额定值: 50mA, 12V DC  
 Insulation resistance: 100MQ min, 100V DC  
 绝缘电阻: 100MQmin, 100V DC  
 Dielectric strength: 250V AC for 1 min  
 介电强度: 250V AC 1分钟  
 Contact resistance: 100mΩ max  
 Travel: 0.25±0.1mm  
 行程: 0.25±0.1mm  
 Lifetime: 600000 times  
 寿命: 600000 times  
 Operating force: 350±50gf  
 操作力: 350±50gf  
 Operating temperature rang: -30°C to + 85°C  
 工作温度范围: -30°C to + 85°C



CIRCUIT DIAGRAM  
电路图

NO 序号	Part name 部件名	Material 材料	QTY 数量	Remark 备注
5	Terminal 端子	Brass 黄铜	4	Ag plating 镀银
4	Base 基座	PA6T	1	Black 黑色
3	Contact 弹片	SUS	1	Ag plating 镀银
2	Stem 按钮	PA6T	1	Yellow 黄色
1	Cover 盖板	Brass 黄铜	1	

REV	DATE	REVISION	DESCRIPTION	ISSUE
A4				
A3				
A2				
A1				



COMMON TOLERANCE

X.XX	± 0.10
X.X	± 0.15
X	± 0.25
ANGULAR	—

UNIT	MM	PROJECTED	PRODUCT NAME:
DRAWN BY	FUYUAN	CHECKED BY	COCO
DATE	2019	APPROVAL B	ALEN
<b>ROCPCU TECHNOLOGY CO., LTD</b>			
Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission			

PRODUCT NAME:

MODEL NO: TP10723580

Https: www.rocpcu.tw