




CIRCUIT DIAGRAM

1. Maximum rating: 50mA 12V DC
1.最大额定值: 50mA 12V DC
Minimum rating: 10µA 1V DC
最小额定值: 10µA 1V DC
2. Insulation resistance: ≥ 100M Ω
2.绝缘电阻: ≥100MΩ
3. Contact resistance: ≤ 100m Ω
3.接触电阻: ≤100mΩ
4. Withstand voltage: 250V AC
4.耐压: 250V AC
5. Operating temperature: - 20 °C ~ + 70 °C
5.使用温度: -20°C ~ + 70°C
6. Action force: 260 ± 50gf
6.动作力: 260±50gf
7. Service life: 1,000,000 times
7.寿命: 1,000,000次
8. Stroke: 0.35 ± 0.10mm
8.行程: 0.35±0.10mm



P.C.B LAND DIMENSION



6	Terminal 端子	BASS 黄铜	4	Ag plating 镀银
5	Housing 外壳	SUS	1	
3	Handle 按柄	silica gel 硅胶	1	Blue 蓝色
2	Shrapnel 弹片	SUS	1	Ag plating 镀银
1	Base 基座	PA46	1	Black 黑色
NO 序号	Part name 部件名	Material 材料	QTY 数量	Remark 备注

A4				
A3				
A2				
A1				
REV	DATE	REVISION	DESCRIPTION	ISSUE



COMMON TOLERANCE

X.XX	± 0.10
X.X	± 0.15
X	± 0.25

ANGULAR

UNIT	MM	PROJECTED		PRODUCT NAME:
DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP11122643
DATE	2019	APPROVAL B	ALEN	Https: www.rocpu.tw
ROCPCU TECHNOLOGY CO.,LTD				
Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission				