



- NOTES:
- 1.Rat voltage:12VDC 50mA
  - 1.额定电压: 12VDC 50mA
  - 2.Contact Resistance:≤100mΩ Max
  - 2.接触电阻: ≤100mΩ
  - 3.Operating Force:260±50gf
  - 3.操作力: 260±50gf
  - 4.Travel: 0.25±0.1mm
  - 4.行程: 0.25 + 0.1mm
  - 5.Insulation Resistance:≥100MΩ
  - 5.绝缘电阻: ≥100MΩ
  - 6.Dielectric strength: ≥250VAC
  - 6.介电强度: ≥250VAC
  - 7.Life: 30,000 times
  - 7.寿命: 30,000 times
  - 8.Operating Temperature:-20℃±80℃
  - 8.使用温度: -20℃±80℃

5	Push-Button 按钮	PPA	1	Black 黑色
4	Blind flange 盖板	SUS	1	
3	Shrapnel 弹片	SUS	1	Ag plating 镀银
2	Noumenon 本体	PPA	1	Black 黑色
1	Card 卡件	Brass	1	Ag plating 镀银
NO 序号	Part name 部件名	Material 材料	QTY 数量	Remark 备注

A4				
A3				
A2				
A1				
REV	DATE	REVISION	DESCRIPTION	ISSUE



COMMON TOLERANCE	
X.XX	± 0.10
X.X	± 0.15
X	± 0.25
ANGULAR	—

UNIT	MM	PROJECTED		PRODUCT NAME:
DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP11822615
DATE	2019	APPROVAL B	ALEN	Https: www.rocpu.tw
<b>ROCPCU TECHNOLOGY CO.,LTD</b>				
Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission				