




PCB.焊接图
PCB.WELDING DRAWING





电路图
CIRCUIT DIAGRAM



NOTES:

1. Rate voltage: 50mA DC12V
1. 额定电压: 50mA DC12V
2. Contact resistance: $\leq 100m\Omega$
2. 接触电阻: $\leq 100m\Omega$
3. Operating force: $160 \pm 50gf$
3. 按力: $160 \pm 50gf$
4. Travel: $0.30 \pm 0.15mm$
4. 行程: $0.30 \pm 0.15mm$
5. Insulated resistance: $\geq 100m\Omega$
5. 绝缘电阻: $\geq 100m\Omega$
6. Dielectric strength: $\geq 250VAC$
6. 介电强度: $\geq 250VAC$
7. life: 50000times
7. 寿命: 50000次
8. working temperature: $-20^{\circ}C \sim 80^{\circ}C$
8. 工作温度: $-20^{\circ}C \sim 80^{\circ}C$

5	Push-button 按钮	Silica gel	1	Black 黑色
4	Blind flange 盖板	SUS	1	
3	Shrapnel 弹片	SUS	1	Ag plating 镀银
2	Noumenon 本体	PPA	1	Black 黑色
1	Card 卡件	Brass	1	Ag plating 镀银
NO 序号	Part name 部件名	Material 材料	QTY 数量	Remark 备注

A4				 ROCPCU	COMMON TOLERANCE X.XX ± 0.10 X.X ± 0.15 X ± 0.25 ANGULAR —	UNIT	MM	PROJECTED		PRODUCT NAME:	
A3						DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO:	TP12221625
A2						DATE	2019	APPROVAL B	ALEN	Https:	www.rocpcu.tw
A1						ROCPCU TECHNOLOGY CO.,LTD					
REV	DATE	REVISION	DESCRIPTION			ISSUE	Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission				