



- NOTES:
1. Rate voltage: 50mA DC  
1. 额定电压: 50mA DC
  2. Contact resistance: ≤100mΩ  
2. 接触电阻: ≤100mΩ
  3. Operating force: 260±50gf  
3. 按力: 260±50gf
  4. Travel: 0.20±0.10mm  
4. 行程: 0.20±0.10mm
  5. Insulated resistance: ≥100MΩ  
5. 绝缘电阻: ≥100MΩ
  6. Dielectric strength: ≥250VAC  
6. 介电强度: ≥250VAC
  7. Working temperature: -20°C~80°C  
7. 工作温度: -20°C~80°C
  8. life: 20000times  
8. 寿命: 20000次

|          |                    |                |           |                  |
|----------|--------------------|----------------|-----------|------------------|
| 5        | Push-button<br>按钮  | PAA            | 1         | white<br>白色      |
| 4        | Blind flange<br>盖板 | Yellow metal   | 1         | Ag plating<br>镀银 |
| 3        | Shrapnel<br>弹片     | SUS            | 1         | Ag plating<br>镀银 |
| 2        | Noumenon<br>本体     | PPA            | 1         | Black<br>黑色      |
| 1        | Card<br>卡件         | Yellow metal   | 1         | Ag plating<br>镀银 |
| NO<br>序号 | Part name<br>部件名   | Material<br>材料 | QTY<br>数量 | Remark<br>备注     |

|     |      |          |             |       |
|-----|------|----------|-------------|-------|
| A4  |      |          |             |       |
| A3  |      |          |             |       |
| A2  |      |          |             |       |
| A1  |      |          |             |       |
| REV | DATE | REVISION | DESCRIPTION | ISSUE |



| COMMON TOLERANCE |        |
|------------------|--------|
| X.XX             | ± 0.10 |
| X.X              | ± 0.15 |
| X                | ± 0.25 |
| ANGULAR          | —      |

|   |        |            |      |                      |
|---|--------|------------|------|----------------------|
| UNIT  | MM     | PROJECTED  |      | PRODUCT NAME:        |
| DRAWN BY  | FUYUAN | CHECKED BY | COCO | MODEL NO: TP12422663 |
| DATE  | 2019   | APPROVAL B | ALEN | Https: www.rocpcu.tw |
| <b>ROCPCU TECHNOLOGY CO.,LTD</b>  |        |            |      |                      |
| Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission |        |            |      |                      |