




PCB board installation size



Circuit diagram



Technical requirement

技术要求

1. Rated voltage: 16V (DC)

1.额定电压: 16V (DC)

Rated current: 0.5A

额定电流: 0.5A

2. Insulation resistance: ≥ 50M Ω

2.绝缘电阻: ≥50MΩ

3. Contact resistance: ≤ 200 Ω

3.接触电阻: ≤200mΩ

4. Withstand voltage: AC 250V (50Hz)/min

4.耐压: AC 250V(50Hz)/min

5. Operating force: 90g ± 20g

5.操作力: 90g±20g

6. Service life: 20000 times

6.寿命: 20000次

6	Solder foot 焊锡脚	Brass 黄铜		Ag plating 镀银
5	Base 基座	Nylon 尼龙	1	Black 黑色
4	lid 盖子	Nylon 尼龙	1	Black 黑色
3	Spring 弹簧	SUS	1	
2	Contact 弹片	Silver copper 复银铜	1	Ag plating 镀银
1	Press handle 按柄	POM	1	Black 黑色
NO 序号	Part name 部件名	Material 材料	QTY 数量	Remark 备注

A4				
A3				
A2				
A1				
REV	DATE	REVISION	DESCRIPTION	ISSUE
	A			B



COMMON TOLERANCE

X.XX	± 0.10
X.X	± 0.15
X	± 0.25

ANGULAR

UNIT	MM	PROJECTED		PRODUCT NAME:
DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP70311
DATE	2019	APPROVAL B	ALEN	Https: www.rocpu.tw
ROCPCU TECHNOLOGY CO.,LTD				
Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission				
D	E	F	G	