


Circuit diagram



PCB board installation size

Technical requirement

技术要求

1. Rated voltage: 12V (DC)

1. 额定电压: 12V(DC)

Rated current: 0.5A

额定电流: 0.5A

2. Switching withstand voltage: AC100V for 1 minute

2. 开关耐压: AC100V 1分钟

3. Insulation resistance: $\geq 50M \Omega$

3. 绝缘电阻: $\geq 50M\Omega$

4. Contact resistance: $\leq 100m \Omega$

4. 接触电阻: $\leq 100m\Omega$

5. Operating force: $26g \pm 10g$

5. 操作力: $26g \pm 10g$

6. Switch life: 50000 times

6. 开关寿命: 50000次

6	Slider 滑块	PA9T		Black 黑色
5	Contact foot 接触脚	Brass 黄铜	3	Ag plating 镀银
4	Lid 盖子	Brass 黄铜	1	Ag plating 镀银
3	Reed 簧片	Phosphorous copper 磷铜	1	Ag plating 镀银
2	Swing handle 摆柄	PA9T	1	Black 黑色
1	Base 基座	PA9T	1	Black 黑色
NO 序号	Part name 部件名	Material 材料	QTY 数量	Remark 备注

A4				
A3				
A2				
A1				
REV	DATE	REVISION	DESCRIPTION	ISSUE
		A		B



COMMON TOLERANCE

X.XX	± 0.10
X.X	± 0.15
X	± 0.25

ANGULAR

UNIT	MM	PROJECTED		PRODUCT NAME:
DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP70541
DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw
ROCPCU TECHNOLOGY CO.,LTD				
Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission				