


Installation position drawing  
安装位置图





The circuit principle diagram  
电路原理图

Technical requirement

技术要求

1. Rated voltage: 16V (DC)  
1. 额定电压: 16V(DC)
- Rated current: 0.5A  
额定电流: 0.5A
2. Insulation resistance:  $\geq 50M \Omega$   
2. 绝缘电阻:  $\geq 50M\Omega$
3. Contact resistance:  $\leq 300m \Omega$   
3. 接触电阻:  $\leq 300m\Omega$
4. Operating force:  $35g \pm 10g$   
4. 操作力:  $35g \pm 10g$
5. Service life: 30000 times  
5. 使用寿命: 30000次
6. Operating temperature:  $-10^\circ C \sim +60^\circ C$   
6. 使用温度:  $-10^\circ C \sim +60^\circ C$



5	Soldering pin 焊线脚	Brass	4	Ag plating 镀银
4	foundation bed 基座	PA46	1	Black 黑色
3	spring 弹簧	Phosphorous copper 磷铜	1	Ag plating 镀银
2	lid 盖子	PA46	1	Black 黑色
1	Press handle 按柄	PA9T	4	Black 黑色
NO 序号	Part name 部件名	Material 材料	QTY 数量	Remark 备注

A4				
A3				
A2				
A1				
REV	DATE	REVISION	DESCRIPTION	ISSUE



COMMON TOLERANCE

X.XX	$\pm 0.10$
X.X	$\pm 0.15$
X	$\pm 0.25$
ANGULAR	—

UNIT	MM	PROJECTED		PRODUCT NAME:
DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP71321
DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw
<b>ROCPCU TECHNOLOGY CO.,LTD</b>				
Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission				