



REV.	ECN NO.	REVISED	DATE

NOTE:

1.MATERIAL:

- a.HOUSING:ABS BLACK
- b.CONTACT:Steel
- (SURFACE PLATING: Ni100u"~120u")

SEE ORDERING INFORMATION

2.ELECTRIC:

- a.CONTACT RESISTANCE: 30 MILLIOHMS MAX
- b.INSULATION RESISTANCE: 1000 MEGA OHMS MIN
- c.DIELECTNIC VOLTAGE: 500V AC ONE SEC LEVEL
- d.OPERATING TEMPERATURE: -25° C~ +85° C

ORDERING INFORMATION

**BH-18650-A\*\*\*001**





电池盒

电池型号

DIP 90° TYPE

PLATING:  
A-Au1U"  
J-Ni100U"~120U"  
K-Sn100U"~120U"

MATERIAL:  
1A-PBT BLACK  
1B-PA66 BLACK  
2A-PPA BROWN  
2B-PPA BLACK  
3A-PPS BROWN  
3B-PPS BLACK  
4A-LCP WHITE  
4B-LCP BLACK  
5B-ABS BLACK



PCB Layout Diagram  
Bottom View

UNLESS OTHERWISE SPECIFIED TOLERANCES		<b>MYOUNG 美阳</b> www.meiyangdz.com			
DECIMALS: X :±0.30 X.X :±0.25 X.XX :±0.20 X.XXX :±0.10	ANGLES: X :±1° X.X :±0.5°	DSND	YangFeng	DATE	2018-09-09
WEIGHT:		CHKD	ZhouRuicai	DATE	2018-09-09
SHEET 1 OF 1		APVD	XueShunyong	DATE	2018-09-09
TITLE:		TITLE: 电池盒BH-18650-1J Ni DIP			
PART NO.:		PART NO.: BH-18650-A5BJ001			
DRAW NO.:		DRAW NO.:MY-CP-0087			

2	TERMINAL	1	STEEL, T=0.3MM	Ni-Plating
1	HOUSING	1	ABS	BLACK
NO.	PART NAME	Q'TY	MATERIAL	PLATING & COLOR