



- NOTE 1. FEMALE-COUNTERPART CONNECTOR : MX84B024SF1 (SJ120504)  
 2. APPLICABLE SCREW : JIS B 1122 CROSS RECESSED HEAD TAPPING SCREW M3×6, CLASS 2 (TYPE B)  
 3. THIS ITEM'S MOLDING MATERIAL IS UL94 V-0 FLAMMABILITY STANDARD.

- 注 1. かん合相手メスコネクタ : MX84B024SF1 (SJ120504)  
 2. 推奨取付ネジ JIS B 1122 十字穴付なベタツピンネジ 2種 M3×6  
 3. 本製品の成形材は、燃焼性UL94 V-0です。

3	TERMINAL-L2	12	BRASS	PLATING: Sn	POST-PLATING
2	TERMINAL-L1	12	BRASS	PLATING: Sn	POST-PLATING
1	HOUSING	1	SPS-GF30 (NOTE3)		COLOR: BLACK

符号 NO.	名称 DESCRIPTION	個数 QTY.	材料 MATERIAL	仕上 FINISH	備考 REMARKS
仕様書 (SPECIFICATION) JACS-11205 JAHL-11205		第1版 (ORIGINAL DATE) 10/MAY/2018		尺度 (SCALE) 2:1	シリーズ (SERIES) MX84
一般公差 (GENERAL TOLERANCE)		製図 DR.	名称 (TITLE) MX84B024NF1		
寸法 (DIMENSION)		担当 CHK.	日本航空電子工業株式会社		
角度 (ANGLES)		査閲 APPD.	JAE JAPAN AVIATION ELECTRONICS INDUSTRY, LTD.		
承認 APPD.		承認 APPD.	図面番号 (DRAWING NO.) SJ120503		
単位 (UNIT) : mm		質量 (MASS) 7.0g	版数 (VER.) 1		