




REFERENCE DRAWING



CIRCUIT DIAGRAM



P.C.B LAND DIMENSION

SPECIFICATION

1. Rating: DC 12V 50mA Max
2. Contact resistance: 100mΩ MAX
3. Insulation resistance: 100MΩ Min
4. Dielectric strength: 250VAC/min
5. Operating force: 320gf ± 70gf
6. Operating life: 300,000 cycles

UNSPECIFIED TOLERANCE	未指定的公差
ANGULAR (角度)	±0.5°
16 < L ≤ 63	±0.4
4 < L ≤ 16	±0.3
L ≤ 4	±0.2

NO.(序号)	PART NAME (零件名)	QTY(数量)	MATERIAL (材料)	REMARK (备注)
4	TAPE (防尘胶)	1	PI	
3	CONTACT FORM(弹片)	1	SUS301	Ag plating
2	HOUSING(基座)	1	LCP	
1	TERMINAL(端子)	1	BRASS	Ag plating



D-SWITCH
东莞市德松电子有限公司
D-SWITCH ELECTRONICS CO.,LTD

版本 VER	变更说明 CHANGE DESCRIPTION	日期 DATE	ECN NO.	版本 VERSION	比例尺 SCALE	日期 DATE	品名 TITLE	图号 DRAWING NO
				核准 APPROVED BY	核对 CHECKED BY	绘图 DRAWN BY	DS-TV/CU12-G	XXXXXXX
						赵华玲		