





3D VIEW




P.C.B LAYOUT  
TOP VIEW



NOTES:

1. CONTACT CURRENT RATING: 1A.
2. CONTACT RESISTANCE: 150 mΩ MAX.;
3. INSULATION RESISTANCE: 1000MΩ MIN.;
4. DIELECTRIC WITHSTANDING: 500V AC MIN.;
5. DURABILITY: 5,000 CYCLES MIN.;
6. CONNECTOR MATING FORCES: 30N MAX.;
7. CONNECTOR UNMATING FORCES: 3N MIN.;



③	Other Terminal	4	SUS	Au Plating		
②	Terminal 2#4#	2	Phosphor bronze	Au Plating		
①	Housing	1	LCP	Black		
ITEM	PART NAME	Serial number	QTY.	MATERIAL	FINISHING	REMARK

APPROVALS		DATE		 ELECTRONICS CO.,LTD				
DRAWN	LIUCAN	2023.2.28					TITLE:	PHONE JACKES
APPROVALS							PART NO.	PJ-399M
TOLERANCES ARE		30~以上	±0.30	ANGLE	UNIT: mm	SCALE: 1:1		
		10~30	±0.20					
		5~10	±0.15					
		~ 5	±0.10					
			±2'		DRAWING NO.		PROJ:	
ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.	SHEET 1 OF 1	

_____	A	_____	NEW	_____	_____	_____
ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.