



What can we help you find?

- [Products](#)
- [Industries](#)
- [Resources](#)
- [About TE](#)
- [My Account](#)
- [Innovation](#)
- [Support Center](#)

1-1194907-6 Product Details

- [Share](#)
- [Print](#)
- [Email](#)



Active

SolderSleeve Wire Splices

D-142-50

1-1194907-6

TE Internal Number: 621054-000

Product Highlights [View All](#)

- Low Temperature
- Splice Type = SolderSleeve
- Fluid Resistance = Immersion
- Wire Temperature Rating Range (Max.) = 105°C
- Inside Diameter = 1.40 mm

[Pricing & Availability](#)

[Request Sample](#)

[Add to My Part List](#)

[Buy Product through Distributor](#)

- [Documents](#)
- [Features](#)
- [Compliance](#)

Please Note:

Use the Product Drawing for all design activity

Product Type Features

Product Type	Low Temperature
Splice Type	SolderSleeve

Dimensions

Inside Diameter (mm [in])	1.40 [0.055]
Inside Diameter Fully Recovered (mm [in])	3.60 [0.142]
Length (mm [in])	15.49 [0.609]

Industry Standards

RoHS/ELV Compliance	Not reviewed for ELV/RoHS compliance
Lead Free Solder Processes	Not relevant for lead free process

Environmental

Fluid Resistance	Immersion
------------------	-----------

Conditions for Usage

Wire Temperature Rating Range (Max.)	105°C
--------------------------------------	-------

Other

Brand	Raychem
-------	---------

Related Products

Not quite the product you're looking for?

[Find Similar Products](#)

[View Part in Product Feature Selector](#)

[Check for Tooling](#)

Corporate Information

- [About TE](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)
- [Terms & Conditions](#)
- [Privacy Policy](#)
- [Global Accessibility Statement](#)

Quick Links

- [Distributor Inventory](#)
- [Product Cross Reference](#)
- [Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Knowledge Base](#)
- [Manage Your Account](#)

Keep Me Informed

