


linear dimension(Tolerances Standard GB/T 14486-2008)								—	\square	\perp
variable range	to	over 6 to 10	over 10 to 30	over 30 to 60	over 60 to 100	over 100 to 160	over 160 to	to	over 10 to 100	over 100 to
	6	10	30	60	100	160		10	100	
tolerance	±0.20	±0.30	±0.50	±0.70	±1.00	±1.30	±1.60	0.10	0.30	0.60

REVISION RECORD				
REV.	DESCRIPTION	ECN No.	APPROVED	DATE
A	新发行		CLF	21.03.15



UL/CUL 技术参数 UL/CUL Technical Data					
等级	Use Group		B	C	D
额定电压	Rated Voltage [V]		125	-	150
额定电流	Rated Current [A]		4	-	4
接线范围	Wire Range		28-20		
单/多芯线	Solid/Stranded [AWG]				
耐电压	Withstanding Voltage		1300V/1Min		
IEC 技术参数 IEC Technical Data					
过电压类别	Overvoltage Category		III	III	II
污染等级	Contamination Class		-	2	2
额定电压	Rated Voltage [V]		-	160	320
额定电流	Rated Current [A]		-	5	5
额定冲击电压	Impulse withstand voltage ^a [KV]		-	2.5	2.5
导线截面积	Conductor cross section		0.5		
硬质/柔性导线	Solid/flexible [mm ²]				
材料 Material					
绝缘材料	Insulation Material		PA66		
阻燃等级	Imflamability		UL94V-0		
导体材料	Contacting Material		铜合金 Copper alloy		
导体表面镀层	Contactive Coating		镀镍 Ni plated		
一般参数 Other Data					
间距	Pitch [mm]		2.54		
极数	Poles [P]		2-24		
剥线长度	Stripping Length [mm]		5-6		
螺丝	Screw/扭矩 Torque(Max) [N.m]		M1.6/0.1		
工作温度	Operating temperatur [°C]		-40~+105		
引针尺寸	Pin Dimensions [mm]		-		
PCB板孔径	PCB Hole Diameter [mm]		-		

DES.	FZM	DATE	21.03.15	单位/UNITS	mm	尺寸/SIZE	A4	比例/SCALE	1:1	第三视角/THIRD ANGLE PROJECTION	版本/REV	A
CHK.	SY	DATE	21.03.15	 慈溪市科发电子有限公司 CIXI KEFA ELECTRONIC CO., LTD				名称/TITLE	KF2EDGK-2.54			
APP.	CLF	DATE	21.03.15									