


**Kinghelm**<sup>®</sup>

| REVISIONS |        |             |       |     |      |
|-----------|--------|-------------|-------|-----|------|
| REV       | NUMBER | DESCRIPTION | DWN   | CHK | DATE |
| A         |        | DESIGN      | James |     | 9/26 |



**NOTES:**

1. ELECTRICAL:
  - 1.1. VOLTAGE RATING:DCV 300V 10MS
  - 1.2. CONDUCTANCE RESISTANCE: 3.0 OHM/MAX.
  - 1.3. INSULATION RESISTANCE: 5.0M OHM/MIN.
  - 1.4. THE CABLE SHOULD BE 100% ELECTRICAL TEST
  - 1.5. IT SHOULD BE NO ANY OPEN/SHORT, MISWIRING AND INTERMITTENT FAILURES.
2. MATERIAL:
  - 2.1. SEE TABLE
3. ALL COMPONENTS ARE RoHS COMPLIANT.

| ITEM NO. | PART NUMBER | DESCRIPTION            | QTY. |
|----------|-------------|------------------------|------|
| ④        | 套管          | OD:2.5* 15 mm 黑色热缩套管   | 1    |
| ③        | 接头          | SMA母头,母针, 4孔法兰, 镀金     | 1    |
| ②        | 端子          | 高仿I-PEX ,1.13端子, 镀金    | 1    |
| ①        | 同轴线         | RG-1.13 黑色线 ,OD:1.10MM | AS   |

金航标电子有限公司

|   |  |               |  |
|---|--|---------------|--|
| ALL DIMENSION ARE IN MM                                       | DRAWN James  | DATE 2023-3-1 | TITLE<br>KH-FLSMA-IPEX113-120(镀金四孔法兰SMA转1代IPEX 1.13黑色线线长120MM) |
|   | CHKD. Frank  | 2023-3-1      |  |
| COMPUTER GENERATED IN SOLIDWORKS<br>DO NOT SCALE THIS DRAWING | APPD. Scott  | 2023-3-1      |  |
| PROJECTION  | GENERAL TOLERANCE FOR ANGLES X.X X.XX X.XXX<br>±1° ±0.3 ±0.25 ±0.150 |               | SIZE B   |
| CUSTOMER P/N:   |  |               | DWG Number.  |
|   |  |               | REV A  |
|   | SCALE:Free   | TYPE          | SHEET 1 OF 1   |