


TABLE:

No.OF PIN	A	B	C
006=2*3PIN	10.16	5.08	13.12
008=2*4PIN	12.70	7.62	15.66
010=2*5PIN	15.24	10.16	18.20
012=2*6PIN	17.78	12.70	20.74
014=2*7PIN	20.32	15.24	23.28
016=2*8PIN	22.86	17.78	25.82
018=2*9PIN	25.40	20.32	28.36
020=2*10PIN	27.94	22.86	30.90
022=2*11PIN	30.48	25.40	33.44
024=2*12PIN	33.02	27.94	35.98

NOTES:

- 1.FINISH:
- 1.1 HOUSING: LCP BLACK,UL94V-0
- 1.2 CONTACT:C7025,GOLD(SEE P/N)PLATED IN CONTACT AERA,80u" MIN MATTE TIN PLATED IN SOLDER AREA, 50u"MIN.NICKEL UNDERRPLATED OVERALL.
- 2.ELECTRICAL:
- 2.1 CURRENT RATING:12Amp;
- 2.2 DIELECTRIC WITHSTANDING VOLTAGE:750V AC/DC.
- 2.3 CONTACT RESISTANCE:20mΩ MAX.
- 2.4 INSULATION RESISTANCE:1000MΩ MIN.
- 2.5 OPERATION TEMPERATURE:-40°C TO+105°C.
- 3.ALL MATERIALS MUST BE ROHS MATERIALS

SCALE: 1:1	UNIT: mm	Title: Card Edge 2.54mm Pitch 2×10Pin			
SIZE: A4		Molde Code: GT-CEDVA-20P-01			
Unless otherwise General tolerance:		DRAWN	CHECKED	APPROVED	DATE
X.	±0.50	Xia	Chen	Chen	2023.02.01
X.x	±0.30				
X.xx	±0.20				
Angles	±5°				



REV: A0 SHEET: 1/1