

3.96 条形连接器 (3.96mm)

技术参数 TECHNICAL PARAMETER

间距(PITCH):3.96mm

极数(Poles):2--16

适用基板厚度(Applicable PC board thickness):1.6mm

额定电流(Current rating):5A,AC,DC

额定电压(Voltage rating):250V,AC,DC

工作温度(Working Temperature):-25°C~+85°C

耐压值(Withstand voltage):1500V,AC/min

接触电阻(Contact resistance): $\leq 0.01 \Omega$

绝缘电阻(Insulation resistance): $\geq 1000M \Omega$

极数 Poles	编号 Part Number	尺寸 Dimension(mm)	
		A	B
2	3.96-2A(W/T)	3.96	8
3	3.96-3A(W/T)	7.92	12
4	3.96-4A(W/T)	11.88	16
5	3.96-5A(W/T)	15.84	20
6	3.96-6A(W/T)	19.80	24
7	3.96-7A(W/T)	23.76	28
8	3.96-8A(W/T)	27.72	32
9	3.96-9A(W/T)	31.68	36
10	3.96-10A(W/T)	35.64	40
11	3.96-11A(W/T)	39.60	44
12	3.96-12A(W/T)	43.56	48
13	3.96-13A(W/T)	47.52	52
14	3.96-14A(W/T)	51.48	56
15	3.96-15A(W/T)	55.44	60
16	3.96-16A(W/T)	59.40	64

材料 MATERIAL

基座(HOUSING):尼龙66UL94V-0(NYLON66 UL94V-0)
 插针(PIN):黄铜(BRASS)表面镀纯锡(PURE TIN-PLATED)

