



REV.	ECON. NO.	DESCRIPTION	DATE	DESIGN
A		变更料号	16/11/22	苏亮

Specifications:
 Current rating: 3A AC/DC.
 Voltage rating: 250V AC/DC
 Temperature range: -40°C~+105°C.
 Contact resistance: 10mΩ Max.
 Insulation resistance: 1000MΩ Min.
 Withstanding voltage: 800V AC/minute.
 Material: pd9t 94v0.

P.C.B LAYOUT



PART NO.	Dimensions	
	A	B
2X02P	6.00	2.00
2X03P	8.00	4.00
2X04P	10.00	6.00
2X05P	12.00	8.00
2X06P	14.00	10.00
2X07P	16.00	12.00
2X08P	18.00	14.00
2X09P	20.00	16.00
2X10P	22.00	18.00
2X11P	24.00	20.00
2X12P	26.00	22.00
2X13P	28.00	24.00
2X14P	30.00	26.00
2X15P	32.00	28.00
2X16P	34.00	30.00
2X17P	36.00	32.00
2X18P	38.00	34.00
2X19P	40.00	36.00
2X20P	42.00	38.00



2P视图

CNJM Joint More Precision electronics Co., Ltd.

DRAW. NO.	DATE	P/N NO.	DRAW. NAME:
DESIGN: 陈雪峰	2017/06/03	CNJM2006WV-S-2XNP	2.0mm PITCH 180° DUAL ROW WAFER -SMT TYPE
CHECK: 杨 烨			
REVIEW:		REV. A/1	SCALE: 1:1
			UNIT: mm
			SHEET: 1 OF 1

DIM	TOL	DIM	TOL
X	/	X*	/
XX	0.25	XX*	
XXX	0.15	XXX*	
XXX	0.10	XXX*	