




| REV. | ECON NO. | DESCRIPTION | DATE | DESIGN |
|------|----------|-------------|------|--------|
| A | | | | |

NOTES:
 CURRENT RATING: 2A AC/DC.
 VOLTAGE RATING: 125V AC/DC
 TEMPERATURE RANGE: -40°C~+105°C.
 CONTACT RESISTANCE: 20MΩ Max.
 INSULATION RESISTANCE: 1000MΩ Min.
 WITHSTANDING VOLTAGE: 800V AC/MINUTE.
 MATERIAL: PA66+GF15%. UL94V-0.



| PART NO. | DIMENSION | |
|-------------|-----------|-------|
| | A | B |
| A2004WR-02P | 2.00 | 6.00 |
| A2004WR-03P | 4.00 | 8.00 |
| A2004WR-04P | 6.00 | 10.00 |
| A2004WR-05P | 8.00 | 12.00 |
| A2004WR-06P | 10.00 | 14.00 |
| A2004WR-07P | 12.00 | 16.00 |
| A2004WR-08P | 14.00 | 18.00 |
| A2004WR-09P | 16.00 | 20.00 |
| A2004WR-10P | 18.00 | 22.00 |
| A2004WR-11P | 20.00 | 24.00 |
| A2004WR-12P | 22.00 | 26.00 |
| A2004WR-13P | 24.00 | 28.00 |
| A2004WR-14P | 26.00 | 30.00 |
| A2004WR-15P | 28.00 | 32.00 |

Recommended P.C.B Layout(Top Side)



CNJM Joint More Precision electronics Co.,Ltd.

| DIM | TOL | DIM | TOL |
|------|------|------|-----|
| X | / | X. | / |
| XX | 0.25 | XX | |
| XXX | 0.15 | XXX | |
| XXXX | 0.10 | XXXX | |

| DRAW. NO. | DATE | P/N NO. | DRAW. NAME: |
|-------------|------------|------------|-------------------|
| | | | |
| DESIGN: 陈雪峰 | 2017.06.03 | A2004WR-NP | 2.0mm pitch wofar |
| CHECK: 杨 烨 | | | |
| REVIEW: | | REV. A/1 | SCALE 1:1 |
| | | | UNIT: mm |
| | | | SHEET: 1 OF 1 |