






| REV. | ECN NO. | DESCRIPTION | DATE | DESIGN |
|------|---------|-------------|------|--------|
| A | | | | |




| PART NO. | DIMENSION | |
|-------------|-----------|-------|
| | A | B |
| A2004WV-02P | 2.00 | 6.00 |
| A2004WV-03P | 4.00 | 8.00 |
| A2004WV-04P | 6.00 | 10.00 |
| A2004WV-05P | 8.00 | 12.00 |
| A2004WV-06P | 10.00 | 14.00 |
| A2004WV-07P | 12.00 | 16.00 |
| A2004WV-08P | 14.00 | 18.00 |
| A2004WV-09P | 16.00 | 20.00 |
| A2004WV-10P | 18.00 | 22.00 |
| A2004WV-11P | 20.00 | 24.00 |
| A2004WV-12P | 22.00 | 26.00 |
| A2004WV-13P | 24.00 | 28.00 |
| A2004WV-14P | 26.00 | 30.00 |
| A2004WV-15P | 28.00 | 32.00 |

NOTES:
 CURRENT RATING:2A AC/DC.
 VOLTAGE RATING:125V AC/DC
 TEMPERATURE RANGE:-40°C~+105°C.
 CONTACT RESISTANCE:20MΩ Max.
 INSULATION RESISTANCE:1000MΩ Min.
 WITHSTANDING VOLTAGE: 800V AC/MINUTE.
 MATERIAL:PA66GF15%.UL94V-0.



Recommended P.C.B Layout(Top Side)



| DIM | TOL | DIM | TOL |
|-------|------|--------|-----|
| X. | / | X' | / |
| X.X | 0.25 | X.X' | |
| X.XX | 0.15 | X.XX' | |
| X.XXX | 0.10 | X.XXX' | / |

CNJM Joint More Precision electronics Co.,Ltd.

| | | | |
|-------------|------------|------------|-------------------|
| DRAW NO. | DATE | P/N NO: | DRAW NAME: |
| DESIGN: 陈雪峰 | 2017.06.03 | A2004WV-NP | 2.0mm pitch wafer |
| CHECK: 杨焯 | | | |
| REVIEW: | | REV. A/1 | SCALE 1:1 |
| | | UNIT: mm | SHEET: 1 OF 1 |