




序号	变更内容	日期	版本
1			
2			



Circuits	Part NO	Dimension(mm)	
		A	B
2	3961H-2P	3.96	8.76
3	3961H-3P	7.92	12.72
4	3961H-4P	11.88	16.68
5	3961H-5P	15.84	20.64
6	3961H-6P	19.80	24.60
7	3961H-7P	23.76	28.56
8	3961H-8P	27.72	32.52
9	3961H-9P	31.68	36.48
10	3961H-10P	35.64	40.44
11	3961H-11P	39.60	44.40
12	3961H-12P	43.56	48.36
13	3961H-13P	47.52	52.32
14	3961H-14P	51.48	56.28
15	3961H-15P	55.44	60.24
16	3961H-16P	59.40	64.20

HOUSING

Part No: 3961H
 Material: Nylon 66 UL94V-2
 Insulation resistance: 1000M OHM /min
 Withstand voltage: 1000V AC/minute
 Voltage rating: 250V AC/DC
 Temperature range: -25°C to $+85^{\circ} \text{C}$

未注公差:
 X.X: ± 0.50
 X.XX: ± 0.25
 X.XXX: ± 0.10

品名:	3961H-XXP	比例	单位	图纸	图号
客户料号:		2:1	mm	1/1	S80387
制图:	刘海平		CKM 深圳市灿科盟实业有限公司 CHANKLEMENT INDUSTRY CO., LTD		
业务:		日期: 2006/10/06			