



Material:
 Insulator: PBT+30% Glass Fiber (UL94V-0).
 Contact: Copper Alloy.
 Contact Plated: Gold or Tin over Nickel Plate.
 Specification:
 Current Rating: 1 Amp.
 Withstanding Voltage: AC 500V for 1 Minute.
 Insulation Resistance: 1000MΩ Min. at DC 500V.
 Contact Resistance: 15mΩ Max..
 Operating Temperature: -40°C ~ +105°C.

Contact Material: Brass

Pos.	Part No.	Dim. A	Dim. B	Dim. C	Dim. D
8	300F-8P 无耳	7.62	15.61	20.41	8.89
10	300F-10P 无耳	10.16	18.15	22.95	11.43
14	300F-14P 无耳	15.24	22.94	28.03	16.51
16	300F-16P 无耳	17.78	25.48	30.57	19.05
20	300F-20P 无耳	22.86	30.56	35.65	24.13
24	300F-24P 无耳	27.94	35.64	40.73	29.21
26	300F-26P 无耳	30.48	38.18	43.27	31.75
30	300F-30P 无耳	35.56	43.26	48.35	36.83
34	300F-34P 无耳	40.64	48.34	53.43	41.91
40	300F-40P 无耳	48.26	55.96	61.05	49.53
50	300F-50P 无耳	60.96	68.66	73.75	62.23
60	300F-60P 无耳	73.66	81.36	86.45	74.93
64	300F-64P 无耳	78.74	86.44	91.53	80.01

TOLERANCE TABLE

.0	±0.30
.00	±0.20
.000	±0.05

APPROVED:

DATE:

CHECKED:

DATE:

DRAWN:

DATE:

SXA

2019-04-27

TITLE:

300F-XP 压线式 无耳 灰白色

深圳市矽科盟实业有限公司
 kintw CHANKEMENG INDUSTRYCO., LTD

CLIENT P/N B-3000FXXP-0800

UNIT	mm	SCALE	Free	REV.	Q700
FILE NO.	Chkntw-300-0009				