



SPECIFICATION:

Current Rating:3.0AMP

Contact Resistance:20m Ω (max)

Insulation Resistance:1000M Ω Min at 500V DC

Dielectric Strength:500V AC Per 1 Minute

Operating Temperature:-40℃ TO +105℃

MATERIALS:

Insulator: P.B.T.+30% Glass Fibre(UL 94V-0)

Contact:Brass

Contact plated: 0.8u" Gold Over Nickel

Poles	Part No.	Dimension mm		
		A	B	C
8	310S-8P	29.36	7.62	16.06
10	310S-10P	31.90	10.16	18.60
12	310S-12P	34.44	12.70	21.14
14	310S-14P	36.98	15.24	23.68
16	310S-16P	39.52	17.78	26.22
18	310S-18P	42.06	20.32	28.00
20	310S-20P	44.60	22.86	31.30
24	310S-24P	49.68	27.94	36.38
26	310S-26P	52.22	30.48	38.92
30	310S-30P	57.30	35.56	44.00
34	310S-34P	62.38	40.64	49.08
40	310S-40P	70.10	48.26	56.70
50	310S-50P	82.70	60.96	69.40
60	310S-60P	95.40	73.66	82.10
64	310S-64P	100.48	78.74	87.18

TOLERANCE TABLE	
.0	±0.30
.00	±0.20
.000	±0.05

APPROVED:	DATE:	Ckmtw 深圳市灿科盟实业有限公司 CHANKEMENG INDUSTRYCO.,LTD			
CHECKED:	DATE:	TITLE: 310S-XP			
DRAWN: LYF	DATE: 2008-04-07	CLIENT P/N		/	
		UNIT	mm	SCALE	free
		FILE NO.	Ckmtw-310-00001	REV.	A