



**SPECIFICATIONS**

Current rating: 3A AC/DC  
 Voltage rating: 250V AC/DC  
 Contact resistance: 20mΩ max.  
 Withstand voltage: 1000V AC/min  
 Insulation resistance: 1000MΩ/min.  
 Temperature range: -25°C~+85°C  
 Applicable PC board thickness: 0.063"(1.6)

Material:

Part No: 2~16

Post: Brass, Tin/plated

Base: Nylon66 UL94V-2

Poles	Part No.	Dimension mm	
		A	B
2	2501R-2P	2.50	7.50
3	2501R-3P	5.00	10.00
4	2501R-4P	7.50	12.50
5	2501R-5P	10.00	15.00
6	2501R-6P	12.50	17.50
7	2501R-7P	15.00	20.00
8	2501R-8P	17.50	22.50
9	2501R-9P	20.00	25.00
10	2501R-10P	22.50	27.50
11	2501R-11P	25.00	30.00
12	2501R-12P	27.50	32.50
13	2501R-13P	30.00	35.00
14	2501R-14P	32.50	37.50
15	2501R-15P	35.00	40.00
16	2501R-16P	37.50	42.50

**TOLERANCE TABLE**

.0	±0.30
.00	±0.20
.000	±0.05

APPROVED: \_\_\_\_\_ DATE: \_\_\_\_\_

CHECKED: \_\_\_\_\_ DATE: \_\_\_\_\_

DRAWN: \_\_\_\_\_ DATE: \_\_\_\_\_

YAN \_\_\_\_\_ DATE: 2012-07-02

TITLE: 2501R-XP 带定位

深圳市灿科盟实业有限公司  
 CKMTW CHANKLEMENT INDUSTRYCO., LTD

PROD. P/N	/
UNIT	mm
SCALE	free
FILE NO.	CKmtw-2501-0017
REV.	A
REV.	KL00