





P. C. B LAYOUT

SPECIFICATION

Poles: 2-24
 Voltage rating: AC, DC 250V
 Current rating: AC, DC, 7A
 Withstand voltage: 1500V AC min.
 Insulation resistance: 1000M Ω min.
 Temperature range: -25°C ~ +85°C
 Applicable PC board thickness: 0.031" ~ 0.063"
 (0.8 ~ 1.6mm)
 Contact resistance: Initial value 10m Ω max.
 After environmental testing 20m Ω max.
 Material: Nylon66 UL94V-2
 Contact: Brass
 Finish: Tin-plated
 Color: Nature

TOLERANCE TABLE

.0	±0.20
.00	±0.10
.000	±0.05

APPROVED:	DATE:	 深圳市灿科盟实业有限公司 CHANKLEMENT INDUSTRYCO., LTD	TITLE:			
CHECKED:	DATE:		5557S-2*XP 方针			
DRAWN:	DATE:	CLIENT P/N / UNIT mm SCALE free FILE NO. Chantw-5557-0015				
LYP	2008-04-07		REV.	A		