




REVISION RECORD				
REV	ECN	DESCRIPTION	DRAFT	DATE



2EDGKAM - 5.0/5.08 - XXP - 1Y - 00A (H)
 (Series No.) (Pitch) (Poles) (Single Pitch)
 (Color): 1.(Grey) 2.(Blue) 3.(Black) 4.(Green) 5.(Orange)
 6.(Red) 7.(Transparent) 8.(Yellow) 9.(White)
 00A-(Standard) (RoHS)

02P: Clasp on the right from this view

- NOTES1:
 UL Standard
 1. Rated voltage/current : 300V / 15A
 2. Withstanding voltage : AC1600V/1Min.
 3. Torque value : M2.5 , 3.54Lb.in
 4. Wire range : 28~12AWG
 IEC Standard

Pollution Degree	2
Overvoltage Category	III
Rate Impulse Voltage(KV)	4.0KV
Rate Voltage(V)	320V
Rate Current(A)	18A

1. Torque value : M2.5 , 0.4N*m
 2. Wire range : 2.5mm²

NOTES2:

1. Dimension shall be interpreted per ASME Y14.5-2009
 2. Pitch : 5.0/5.08mm, Poles : N=02~22P
 3. Stripping length : 7~8mm
 4. Operating temperature : -40°C~+105°C
 5. Undimensioned tolerances:

mm	Over	Over	Over	Over	Over
Pitch range in	10	30	60	100	150
mm	TO	TO	TO	TO	TO
±0.15	±0.20	±0.30	±0.50	±0.70	±1.00
±1.00	±1.30	±2.00	±3.00	±4.00	±5.00

6. RoHS Compliance

PART NO.:		/	
APPD:		/	
CHKD:		/	
DRAFT:		/	
THIRD ANGLE PROJECTION			
NAME:		宁波德森电子有限公司 NINGBO DEGSON ELECTRICAL CO., LTD	
TITLE:		CUSTOMER DRAWING	
DRAWING NO.:		/	
SCALE:		DO NOT SCALE DRAWING	
REV	REV	SHEET	SCALE
D0	D0	1/1	1:1