





REVISION RECORD				
REV	ECN	DESCRIPTION	DRFT	DATE



NOTES1:


- UL Standard
 1.Rated voltage/current : 150V / 6A
 2.Torque value : M1.6 , 1.29Lb.in
 3.Wire range : 26~18AWG
- IEC Standard
 1.Rated voltage/current : 130V / 8A
 2.Torque value : M1.6 , 0.15N·m
 3.Wire range : 0.5~1.0mm²

NOTES2:

- 1.Dimension shall be interpreted per ASME Y14.5-2009
 2.Pitch : 2.54mm, Poles : N=02-12P
 3.Stripping length : 4~5mm
 4.Withstanding voltage : AC1250V/1Min
 5.Operating temperature: -40°C~+105°C
 6.Undimensioned tolerances:

Pitch range in mm			Nominal dimension range in mm				-	∩	□
TO	Over TO	Over TO	TO	Over TO	Over TO	Over TO	0.1/10		
6	6 TO 10	10 TO 24	30	30 TO 60	60 TO 100	100 TO 150			
	±0.15	±0.20	±0.30	±0.30	±0.50	±0.70	±1.00	±1.30	
								±2'	

7.RoHS Compliance



P.C.B. LAYOUT

DG308 - 2.54 - XXP - 1Y - 00A (H)
 (RoHS)
 00A-(Standard)
 (Series No.) (Pitch) (Poles) (Single Pitch) (Color): 1.(Grey) 2.(Blue) 3.(Black) 4.(Green) 5.(Orange) 6.(Red) 7.(Transparent) 8.(Yellow) 9.(White)

DETACHED LISTS	PART NO.:	/			
	APPD:	NAME: NINGBO DEGSON ELECTRICAL CO., LTD			
	CHKD:	DG308-2.54-XXP-1Y-00A(H)			
	DRFT: YXX 2018/07/13	TITLE: CUSTOMER DRAWING	REV	D0	
		DRAWING NO.:	SHEET	1/1	
	THIRD ANGLE PROJECTION	MM (INCH)	DO NOT SCALE DRAWING	SCALE	1:1

H
G
F
E
D
C
B
A

H
G
F
E
D
C
B
A