



SPECIFICATIONS

- 1、Current Rating: 3A AC, DC
- 2、Voltage Rating: 250V AC, DC
- 3、Temperatuer Range: -25℃~+85℃
- 4、Contact Resistance: 20mΩ Max
- 5、Insulation Resistance: 1000MΩ Min
- 6、Withstanding Voltang: 1000V AC/minute
- 7、Material:Wafer Nylon66, UL94V-0
PIN Brass Tin-plated



PCB LAYOUT

编 号	尺寸 (mm)	
	A	B
5264-2A	2.50	7.50
5264-3A	5.00	10.00
5264-4A	7.50	12.50
5264-5A	10.00	15.00
5264-6A	12.50	17.50
5264-7A	15.00	20.00
5264-8A	17.50	22.50
5264-9A	20.00	25.00
5264-10A	22.50	27.50
5264-11A	25.00	30.00
5264-12A	27.50	32.50
	47.50	52.50

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	钱岳生		料号 PART NO.	5264-NA		版本 REV.	A				
			X.±0.25	X.'±2'		审核 CHECK	2013、07、01		品名 TITLE	5264直针		页次 SHEET	1/1			
			.X±0.20	.X'±1'			核准 APPROVAL			2013、07、03			客户料号 CUTL NO.	WAFER DIP TYPE		
			.XX±0.15	.XX'±0.5'						张名				富港电子		
.XXX±0.10	.XXX'±0.5'	2013、07、05														
			单位 UNITS	MM	比例 SCALE	1:1										