




SPECIFICATIONS

- 1、Current Rating: 3A AC, DC
- 2、Voltage Rating: 100V AC, DC
- 3、Temperatuer Range: $-25^{\circ}\text{C} \sim +85^{\circ}\text{C}$
- 4、Contact Resistance: $20\text{m}\Omega$ Max
- 5、Insulation Resistance: $1000\text{M}\Omega$ Min
- 6、Withstanding Voltang: 800V AC/minute
- 7、Material: Wafer PBT, UL94V-0
PIN Brass Tin-plated




PCB LAYOUT

编 号	尺寸 (mm)	
	A	B
PA-2A	2.00	6.00
PA-3A	4.00	8.00
PA-4A	6.00	10.00
PA-5A	8.00	12.00
PA-6A	10.00	14.00
PA-7A	12.00	16.00
PA-8A	14.00	18.00
PA-9A	16.00	20.00
PA-10A	18.00	22.00
PA-11A	20.00	24.00
PA-12A	22.00	26.00
	30.00	34.00



7~9A



10~16A

GENERAL TOLERANCE		制 图	钱岳生		料号	PA-NA		版本	A
X.±0.25	X.*±2'	DRAWING	2021、05、03		PART NO.	PA直针		REV.	
.X±0.20	.X*±1'	审 核	张名		品名	WAFER DIP TYPE		页次	1/1
.XX±0.15	.XX*±0.5'	CHECK	2021、05、04		TITLE			SHEET	
.XXX±0.10	.XXX*±0.5'	核 准	张名		客户料号			富 港 电 子	
		APPROVAL	2021、05、05		CUTL NO.				
单 位	MM	比 例	1:1						
UNITS	MM	SCALE	1:1						