


### SPECIFICATIONS


- 1、Current Rating: 3A AC, DC
- 2、Voltage Rating: 100V AC, DC
- 3、Temperatuer Range: -25°C~+85°C
- 4、Contact Resistance: 20mΩ Max
- 5、Insulation Resistance: 1000MΩ Min
- 6、Withstanding Voltang: 800V AC/minute
- 7、Material:Wafer PBT, UL94V-0  
PIN Brass Tin-plated

编 号	尺寸 (mm)	
	A	B
PA-2AWD	2.00	6.00
PA-3AWD	4.00	8.00
PA-4AWD	6.00	10.00
PA-5AWD	8.00	12.00
PA-6AWD	10.00	14.00
PA-7AWD	12.00	16.00
PA-8AWD	14.00	18.00
PA-9AWD	16.00	20.00
PA-10AWD	18.00	22.00
PA-11AWD	20.00	24.00
PA-12AWD	22.00	26.00
	30.00	34.00

### PCB LAYOUT



7~9A



10~16A

GENERAL TOLERANCE		制 图 DRAWING 2021、05、03	料 号 PART NO. PA-NAW	版 本 REV. A	客 户 料 号 CUTL. NO.	富 港 电 子						
X.±0.25	X.*±2'						审 核 CHECK 2021、05、04	品 名 TITLE PA弯针 WAFER DIP TYPE	页 次 SHEET 1/1			
.X±0.20	.X*±1'									核 准 APPROVAL 2021、05、05	单 位 UNITS MM	比 例 SCALE 1:1
.XX±0.15	.XX*±0.5'											
.XXX±0.10	.XXX*±0.5'											