





版本 REV.	日期 DATE	ECN NO.	变更内容 DESCRIPTION	制图 DRAWN



SPECIFICATIONS

- 1、Current Rating: 3A AC, DC
- 2、Voltage Rating: 300V AC, DC
- 3、Temperatuer Range: -25℃~+85℃
- 4、Contact Resistance: 20mΩ Max
- 5、Insulation Resistance: 1000MΩ Min
- 6、Withstanding Voltang: 800V AC/minute
- 7、Material: Wafer Nylon6T, UL94V-0
PIN Brass Tin-plated
Solder tab Brass Tin-plated



PCB LAYOUT

编 号	尺寸 (mm)	
	A	B
PAE-2AWT	2.00	8.00
PAE-3AWT	4.00	10.00
PAE-4AWT	6.00	12.00
PAE-5AWT	8.00	14.00
PAE-6AWT	10.00	16.00
PAE-7AWT	12.00	18.00
PAE-8AWT	14.00	20.00
PAE-9AWT	16.00	22.00
PAE-10AWT	18.00	24.00
PAE-11AWT	20.00	26.00
PAE-12AWT	22.00	28.00
	28.00	34.00

GENERAL TOLERANCE		制 图 DRAWING	钱岳生 2014、07、01	料 号 PART NO	PAE-NAWT	版 本 REV.	A
X.±0.25	X.*±2'	审 核 CHECK	张 名 2014、07、03	品 名 TITLE	PAE贴片 WAFER-SMT TYPE	页 次 SHEET	1/1
.X±0.20	.X*±1'	核 准 APPROVAL	张 名 2014、07、05	客 户 料 号 CUTM NO		富 港 电 子	
.XX±0.15	.XX*±0.5'	单 位 UNITS	MM	比 例 SCALE	1:1		
.XXX±0.10	.XXX*±0.5'						