



**SPECIFICATIONS**

- 1、Current Rating: 3A AC, DC
- 2、Voltage Rating: 250V AC, DC
- 3、Temperatuer Range: -25°C~+85°C
- 4、Contact Resistance: 20mΩ Max
- 5、Insulation Resistance: 1000MΩ Min
- 6、Withstanding Voltang: 800V AC/minute
- 7、Material: Wafer Nylon66, UL94V-0  
PIN Brass(H65) Tin-plated

编号	尺寸 (mm)		
	A	B	C
PHD-2*2A	2.00	6.00	
PHD-2*3A	4.00	8.00	
PHD-2*4A	6.00	10.00	
PHD-2*5A	8.00	12.00	
PHD-2*6A	10.00	14.00	
PHD-2*7A	12.00	16.00	
PHD-2*8A	14.00	18.00	
PHD-2*9A	16.00	20.00	
PHD-2*10A	18.00	22.00	
PHD-2*11A	20.00	24.00	
PHD-2*12A	22.00	26.00	
PHD-2*13A	24.00	28.00	
PHD-2*14A	26.00	30.00	
PHD-2*15A	28.00	32.00	
PHD-2*16A	30.00	34.00	
PHB-2*17A	32.00	36.00	
PHD-2*18A	34.00	38.00	
PHD-2*19A	36.00	40.00	
PHD-2*20A	38.00	42.00	

**PCB LAYOUT**

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	钱岳生	料号 PART NO.	PHD-2*NA	版本 REV.	A			
			X.±0.25	X.*±2'		2013、07、01					品名 TITLE	页次 SHEET	1/1
			.X±0.20	.X*±1'		审核 CHECK					张名	客户料号 CUTL NO.	
			XX+0 15	XX*+0 5'		核准 CHECK					张名		

联系电话 18058866958

1:1 深圳市华灿天禄电子有限公司