



PCB LAYOUT

SPECIFICATIONS

- 1、Current Rating: 3A AC, DC
- 2、Voltage Rating: 250V AC, DC
- 3、Temperatuer Range: -25℃~+85℃
- 4、Contact Resistance: 20mΩ Max
- 5、Insulation Resistance: 1000MΩ Min
- 6、Withstanding Voltang: 800V AC/minute
- 7、Material: Wafer Nylon66, UL94V-0
PIN Brass (H65) Tin-plated

编号	尺寸 (mm)		
	A	B	C
PHD-2*2AW	2.00	6.00	
PHD-2*3AW	4.00	8.00	
PHD-2*4AW	6.00	10.00	
PHD-2*5AW	8.00	12.00	
PHD-2*6AW	10.00	14.00	
PHD-2*7AW	12.00	16.00	
PHD-2*8AW	14.00	18.00	
PHD-2*9AW	16.00	20.00	
PHD-2*10AW	18.00	22.00	
PHD-2*11AW	20.00	24.00	
PHD-2*12AW	22.00	26.00	
PHD-2*13AW	24.00	28.00	
PHD-2*14AW	26.00	30.00	
PHD-2*15AW	28.00	32.00	
PHD-2*16AW	30.00	34.00	
PHB-2*17AW	32.00	36.00	
PHD-2*18AW	34.00	38.00	
PHD-2*19AW	36.00	40.00	
PHD-2*20AW	38.00	42.00	

联系电话 18058866958

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	钱岳生 2013. 07. 01	料号 PART NO.	PHD-2*NAW	版本 REV.	A
			X.±0.25	X.'±2'	审核	张名	品名 TITLE	PHB直针 WAFER DIP TYPE	页次 SHEET	1/1
			.X±0.20	.X'±1'	CHECK	2013. 07. 03	客户料号 CUTM. NO.			
			XX+0.15	XX'+0.5'	核准	张名				
						1:1	深圳市华灿天禄电子有限公司			