



编号	尺寸 (mm)	
	A	B
SPH-2*2A	2.00	6.00
SPH-2*3A	4.00	8.00
SPH-2*4A	6.00	10.00
SPH-2*5A	8.00	12.00
SPH-2*6A	10.00	14.00
SPH-2*7A	12.00	16.00
SPH-2*8A	14.00	18.00
SPH-2*9A	16.00	20.00
SPH-2*10A	18.00	22.00
SPH-2*11A	20.00	24.00
SPH-2*12A	22.00	26.00
	38.00	42.00

SPECIFICATIONS

- 1、Current Rating: 3A AC, DC
- 2、Voltage Rating: 250V AC, DC
- 3、Temperatuer Range: -25℃~+85℃
- 4、Contact Resistance: 20mΩ Max
- 5、Insulation Resistance: 1000MΩ Min
- 6、Withstanding Voltang: 800V AC/minute
- 7、Material: Wafer Nylon46, UL94V-0
PIN Brass Tin-plated

PCB LAYOUT

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	钱岳生 2021、05、03	料号 PART NO.	SPH-2*NA	版本 REV.	A
			X.±0.25	X.'±2'	审核 CHECK	张名 2021、05、04	品名 TITLE	SPH直针 WAFER DIP TYPE	页次 SHEET	1/1
			.X±0.20	.X'±1'	核准 APPROVAL	张名 2021、05、05	客户料号 CUTM. NO.			
			.XX±0.15	.XX'±0.5'	单位 UNITS	MM	比例 SCALE	1:1	富港电子	
			.XXX±0.10	.XXX'±0.5'						